

# Tompkins

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

### Description:

Tompkins Collection 52 in. Five Blade Matte Black Coastal Ceiling Fan with Integrated CCT-LED light

### Specifications:

- Clear Hammered Glass Bowl
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box
- Mounting Bracket
- 80 in of wire supplied

### Performance:

Input Power	24 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,900/80 (LM-79)
CCT	2700 K
	3000 K
	5000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed
	Meets California Title 24 JA8-2019
	DC motor

# P250104-31M-CS



### Dimensions:

Diameter: 52 in  
 Height: 17 in

Clear Hammered Glass Bowl



**Side A**  
Matte Black

**Side B**  
Toasted Oak

## ENERGYGUIDE

Estimated  
Yearly Energy Cost

# \$11

\$3

\$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day  
 • Your cost depends on rates and use  
 • Energy Use: 38 Watts

Airflow

# 3,296

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move  
 • Airflow Efficiency: 86 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

**Dimming Notes:**

---

P250104-31M-CS is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

# P250104-31M-CS