

Conte

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

Description:

Conte Collection 52-in Three-Blade Matte Black Contemporary Ceiling Fan with Matte Black Blades

Specifications:

- White Polycarbonate Round
- Canopy covers a standard 4" recessed outlet box

Performance:

Lamp Wattage	20 W
Input Voltage	120 VAC
Lumens/LPW (Delivered)	1,865
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed
	Meets California Title 24 JA8-2022
	AC motor

P250105-31M-30



Shown with included light kit installed.



Dimensions:

Diameter: 52 in
 Height: 14-1/16 in

White Polycarbonate Round
 Width: 5-9/16 in
 Height: 1-5/16 in

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$11

Airflow

3,735

Cubic Feet Per Minute

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- Your cost depends on rates and use
- Energy Use: 38 Watts

All estimates based on typical use, excluding lights

ftc.gov/energy