

# Insigna

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

### Description:

Insigna Collection 60-in Three-Blade Brushed Nickel Contemporary Ceiling Fan with Matte Black Blades

### Specifications:

- Frosted Glass Round
- Canopy covers a standard 4" recessed outlet box

### Performance:

Lamp Wattage	20 W
Input Voltage	120 VAC
Lumens/LPW (Delivered)	1,865
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed
	Meets California Title 24 JA8-2022
	DC motor

# P250107-009-30



### Dimensions:

Diameter: 62 in  
 Height: 14-3/4 in

Frosted Glass Round  
 Width: 5-1/2 in  
 Height: 0-1/8 in

## ENERGYGUIDE

**Estimated  
Yearly Energy Cost**

**\$6**

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 21 Watts

**Airflow**

**4,519**

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 211 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy