

# Paso

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

### Description:

Paso Collection 60-in Three-Blade Matte Black with Matte Black Blades Luxe Industrial Ceiling Fan with 3 Speed Remote Control with Wall Bracket and Battery included

### Specifications:

- Canopy covers a standard 4" recessed outlet box

### Performance:

Input Voltage	120 VAC
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed DC motor

# P250109-31M




### Dimensions:

Diameter: 60 in  
 Height: 16-1/2 in

## ENERGYGUIDE

**Estimated  
Yearly Energy Cost**

# \$6



Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day  
 • Your cost depends on rates and use  
 • Energy Use: 21 Watts

**Airflow**

# 3,659

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move  
 • Airflow Efficiency: 174 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy