

Bisbee

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

Description:

Bisbee Collection 55-in Three-Blade Brushed Nickel Global Ceiling Fan with Matte Black Accent

Specifications:

- White Polycarbonate Round
- Canopy covers a standard 4" recessed outlet box

Performance:

Lamp Wattage	20 W
Input Voltage	120 VAC
Lumens/LPW (Delivered)	1,865
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed
	Meets California Title 24 JA8-2022
	DC motor

P250110-009-30



Dimensions:

Diameter: 55-5/16 in
 Height: 14-3/4 in

White Polycarbonate Round
 Width: 4-11/16 in
 Height: 0-7/8 in

ENERGYGUIDE

Estimated Yearly Energy Cost

\$6

\$3

\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 21 Watts

Airflow

3,635

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move.
- Airflow Efficiency: 170 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy