

Project:		
Fixture Type:		
Location:		
Contact:		

# Belen

Ceiling downrod Mounted • Damp Location Listed PROGRESS LED

## **Description:**

Belen Collection 60-in Three-Blade Brushed Nickel Modern Ceiling Fan with Matte Black Blades

# **Specifications:**

- · White Polycarbonate Round
- · Canopy covers a standard 4" recessed outlet box

#### **Performance:**

Lamp Wattage	20 W	
Input Voltage	120 VAC	
Lumens/LPW (Delivered)	1,865	
CRI	90 CRI	
Life (hours)	50000 (L70/TM-21)	
Warranty	Limited Lifetime Warranty	
Labels	UL Damp Location Listed	
	Meets California Title 24 JA8-2022	
	DC motor	

# P250111-009-30





### **Dimensions:**

Diameter: 60 in Height: 13-9/16 in

White Polycarbonate Round

Width: 4-7/8 in Height: 1-5/16 in

