

Insigna

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

Description:

Insigna Collection 72-in Six-Blade Vintage Brass Contemporary Ceiling Fan with Matte White Blades

Specifications:

- Frosted Glass Round
- Canopy covers a standard 4" recessed outlet box

Performance:

Lamp Wattage	20 W
Input Voltage	120 VAC
Lumens/LPW (Delivered)	1,865
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed
	Meets California Title 24 JA8-2022
	DC motor

P250113-163-30



Dimensions:

Diameter: 72 in
 Height: 14-3/4 in

Frosted Glass Round
 Width: 5-1/2 in
 Height: 0-1/8 in

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$5

\$3

|
|
|
|

\$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • **Your cost depends on rates and use**
 • Energy Use: 18 Watts

Airflow

6,108

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 334 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy