

Project:

Fixture Type:

Location:

Contact:

# Fanin

Ceiling Flush Mounted • Damp Location Listed PROGRESS LED

# **Description:**

Fanin Collection Oscillating Three-Blade Matte Black Luxe Ceiling Fan with Matte Black Blades and Artisanal Glass

## **Specifications:**

- · Frosted Acrylic Lens
- Ceiling Pan covers a standard 4" recessed outlet box: 7.6875 in W., 0.75 in ht.
- 6 in of wire supplied

#### **Performance:**

Lamp Wattage	31 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,398/73.42 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	ETL Damp Location Listed
	Meets California Title 24 JA8-2022
	DC motor

# P250114-31M-30



## **Dimensions:**

Diameter: 19-5/8 in Height: 10-1/8 in

