

Shear

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

Description:

Shear Collection Oscillating Three-Blade Brushed Bronze Ceiling Fan with Gold Blades

Specifications:

- Frosted Acrylic Lens
- Canopy covers a standard 4" recessed outlet box: 7.063 in W., 2.375 in ht.
- 12 in of wire supplied

Performance:

Lamp Wattage	31 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,380/73.84 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	ETL Damp Location Listed Meets California Title 24 JA8-2022
	DC motor

P250115-109-30



Dimensions:

Diameter: 19-5/8 in
 Height: 17-3/4 in

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$4

\$10 | | | \$50

Cost Range of Similar Models (18" or smaller)

- Based on 12 cents per kWh and 6.4 hours use per day
- Your cost depends on rates and use
- Energy Use: 14 Watts

Airflow

413

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 30Cubic Feet Per Minute Per Watt

Model No. :250115

All estimates based on typical use, excluding lights ftc.gov/energy