

Shear

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

Description:

Shear Collection Oscillating Three-Blade Matte black Ceiling Fan with Matte Black Blades

Specifications:

- Frosted Acrylic Lens
- Canopy covers a standard 4" recessed outlet box: 7.063 in W., 2.375 in ht.
- 12 in of wire supplied

Performance:

Lamp Wattage	31 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,380/73.84 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	ETL Damp Location Listed
	Meets California Title 24 JA8-2022
	DC motor

P250115-31M-30



Dimensions:

Diameter: 19-5/8 in
 Height: 17-3/4 in

ENERGYGUIDE	
<p>Estimated Yearly Energy Cost</p> <p>\$4</p> <p>\$10 \$50</p> <p>Cost Range of Similar Models (18" or smaller)</p> <ul style="list-style-type: none"> • Based on 12 cents per kWh and 6.4 hours use per day • Your cost depends on rates and use • Energy Use: 14 Watts 	<p>Airflow</p> <p>413</p> <p>Cubic Feet Per Minute</p> <ul style="list-style-type: none"> • The higher the airflow, the more air the fan will move • Airflow Efficiency: 30Cubic Feet Per Minute Per Watt <p><small>Model No. 250115</small></p>
<small>All estimates based on typical use, excluding lights</small>	
ftc.gov/energy	