

Burnett

Ceiling Flush Mounted • Damp Location Listed **PROGRESS LED**

Description:

Burnett Collection Oscillating Three-Blade Brushed Nickel Modern Traditional Ceiling Fan with Silver Blades and Chrome Accent

Specifications:

- Frosted Acrylic Lens
- Ceiling Pan covers a standard 4" recessed outlet box: 7.6875 in W., 0.75 in ht.
- 6 in of wire supplied

Performance:

Lamp Wattage	32 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,420/73.58 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	ETL Damp Location Listed Meets California Title 24 JA8-2022
	DC motor

P250116-009-30



Dimensions:

Diameter: 20-15/16 in
 Height: 9-3/4 in

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$4

\$10 | | | \$50

Cost Range of Similar Models (18" or smaller)

- Based on 12 cents per kWh and 6.4 hours use per day
- Your cost depends on rates and use
- Energy Use: 14 Watts

Airflow

351

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 25Cubic Feet Per Minute Per Watt

Model No. 250116

All estimates based on typical use, excluding lights ftc.gov/energy