

Belen

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

Description:

Belen Collection 60-in Three-Blade Brushed Nickel Modern Ceiling Fan with Silver Blades

Specifications:

- White Polycarbonate Round
- Canopy covers a standard 4" recessed outlet box

Performance:

Lamp Wattage	20 W
Input Voltage	120 VAC
Lumens/LPW (Delivered)	1,865
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed
	Meets California Title 24 JA8-2022
	DC motor

P250117-009-30



Dimensions:

Diameter: 60 in
 Height: 13-9/16 in

White Polycarbonate Round
 Width: 4-7/8 in
 Height: 1-5/16 in

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$6

\$3

\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 22 Watts

Airflow

4,435

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 206 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy