

Project:
Fixture Type:
Location:

Belen

Ceiling downrod Mounted • Damp Location Listed PROGRESS LED

Contact:

Description:

Belen Collection 60-in Three-Blade Matte Black Modern Ceiling Fan with Matte Black Blades

Specifications:

- · White Polycarbonate Round
- · Canopy covers a standard 4" recessed outlet box

Performance:

Lamp Wattage	20 W
Input Voltage	120 VAC
Lumens/LPW (Delivered)	1,865
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	Limited Lifetime Warranty
Labels	UL Damp Location Listed
	Meets California Title 24 JA8-2022
	DC motor

P250117-31M-30





Dimensions:

Diameter: 60 in Height: 13-9/16 in

White Polycarbonate Round

Width: 4-7/8 in Height: 1-5/16 in

