

oject:	
kture Type:	
cation:	

Beal

Ceiling Flush Mounted • Damp Location Listed PROGRESS LED

Contact:

Description:

36" Ceiling Fan

Specifications:

- Backplate covers a standard 4" recessed outlet box: 8.69 in W., 0.75 in ht., 8.69 in depth
- · Mounting backplate for outlet box included
- · 12 in of wire supplied

Performance:

Input Voltage	120 VAC
Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	1-year Limited Warranty
Labels	ETL Damp Location Listed
	DC



Dimensions:

Diameter: 33-3/16 in Height: 13-15/16 in

