

Beal

Ceiling Flush Mounted • Damp Location Listed **PROGRESS LED**

Description:

36" Ceiling Fan

Specifications:

- Backplate covers a standard 4" recessed outlet box: 8.69 in W., 0.75 in ht., 8.69 in depth
- Mounting backplate for outlet box included
- 12 in of wire supplied

Performance:

Input Voltage	120 VAC
Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	1-year Limited Warranty
Labels	ETL Damp Location Listed
	DC

P250119-31M



Dimensions:

Diameter: 33-3/16 in
 Height: 13-15/16 in

ENERGYGUIDE

<p>Estimated Yearly Energy Cost</p> <h1 style="margin: 0;">\$2.0</h1>	<p>Airflow</p> <h1 style="margin: 0;">1,767</h1> <p>Cubic Feet Per Minute</p>
<p>\$3 \$34</p> <p><small>Cost Range of Similar Models (19" – 84")</small></p> <p><small>• Based on 12 cents per kWh and 6.4 hours use per day</small></p> <p><small>• Your cost depends on rates and use</small></p> <p><small>• Energy Use: 8 Watts</small></p>	<p><small>• The higher the airflow, the more air the fan will move</small></p> <p><small>• Airflow Efficiency: 227 Cubic Feet Per Minute Per Watt</small></p>
<p><small>All estimates based on typical use, excluding lights</small></p>	

ftc.gov/energy