

# Sewell

Ceiling downrod Mounted • Damp Location Listed **PROGRESS LED**

## Description:

Sewell Collection 24-in. Three-Blade Matte Black Modern Ceiling Fan  
 24" Cage Fan

## Specifications:

- Canopy covers a standard 4" recessed outlet box: 7.0625 in W., 2.375 in ht., 7.0625 in depth
- Mounting Bracket
- 12 in of wire supplied

## Performance:

Input Power	5.5 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	500/90 (LM-79)
CCT	2200 K
CRI	80 CRI
Life (hours)	15000 (L70/TM-21)
Warranty	1-year Limited Warranty
Labels	ETL Damp Location Listed Meets California Title 24 JA8-2019
	DC motor

# P250120-31M-WB



## Dimensions:

Diameter: 24 in  
 Height: 19-3/16 in

## ENERGYGUIDE

**Estimated  
Yearly Energy Cost**

\$4

\$10 | | | \$50

Cost Range of Similar Models (18" or smaller)

- Based on 12 cents per kWh and 6.4 hours use per day
- Your cost depends on rates and use
- Energy Use: 13 Watts

**Airflow**

940

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 72 Cubic Feet Per Minute Per Watt

Model No. :250120

All estimates based on typical use, excluding lights [ftc.gov/energy](http://ftc.gov/energy)