

# Brant

Ceiling Flush Mounted • Damp Location Listed **PROGRESS LED**

### Description:

Brant Collection 52-in. Three-Blade Satin White Modern Ceiling Fan  
 52" 3 Blade Fan

### Specifications:

- White Opal Polycarbonate Lens
- Backplate covers a standard 4" recessed outlet box: 8 in W., 0.6875 in ht., 8 in depth
- Mounting backplate for outlet box included
- 12 in of wire supplied

### Performance:

Input Power	20 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,952/90.77 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	1-year Limited Warranty
Labels	UL Damp Location Listed
	Meets California Title 24 JA8-2019
	DC motor

# P250121-028-30



### Dimensions:

Diameter: 52 in  
 Height: 12-1/16 in

White Opal Polycarbonate Lens  
 Diameter: 6 in  
 Height: 1-5/8 in

## ENERGYGUIDE

**Estimated  
Yearly Energy Cost**

# \$8

\$3

\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- Your cost depends on rates and use
- Energy Use: 27 Watts

**Airflow**

# 3,887

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 144 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy