

Project:		
Fixture Type:		
Location:		
Contact:		

# **AIRPRO**

Ceiling downrod mounted • Dry location listed

# **Description:**

52" Signature five-blade ceiling fan with reversible Cherry/Natural Cherry blades, Brushed Nickel finish, and 30 year limited warranty. Powerful AirPro motor features 3-speed control that can also be reversed to provide year-round comfort. Standard canopy is designed for sloped ceilings with 12:12 pitch and a 3/4"x 4-1/2" downrod is included. Can be used to comply with California Title 20.

## **Specifications:**

- · Brushed Nickel (-09) (Plated)
- · Steel construction, aluminum or zinc blade arms
- · 52" AirPro Collection Signature ceiling fan features five reversible blades
- · Reversible Cherry/Natural Cherry blades
- · AirPro Collection Signature ceiling fan with Brushed Nickel finish
- · Pull chain is chrome with cherry fob
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- · AirPro ceiling fan adds form and function by providing increased air circulation in rooms
- Features Transitional design styling
- · Powerful and reversible 3-speed motor control
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- · Compatible with universal light kits
- · UL/CUL dry location listed
- · Dual ceiling mounting on downrod, or close to ceiling
- A 3/4" x 4-1/2" downrod is included. Longer accessory downrods can be ordered separately
- Standard canopy designed for sloped ceilings up to 45 degrees (12:12 ceiling pitch)
- · Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 4306 cfm, Energy consumption- 65 watts (excluding lights), Airflow efficiency- 66 cfm/watt
- · 30 year limited warranty.
- · Canopy covers a standard 4" octagonal recessed outlet box
- · Mounting hardware for outlet box included
- 80" of wire supplied
- $\bullet \quad \hbox{Cherry/Natural Cherry reversible blades, plywood construction}\\$
- · Chrome pull chain with Maple fob
- · 12 degree blade pitch
- Dual-mount for downrod or close-to-ceiling installation
- Three speed control, manual reverse control
- Airflow: 4306 CFM\*
- · Energy consumtion: 65 watts (excluding lights)\*
- Airflow efficiency: 66 cfm/watt\*
- · \* Fan on a downrod

### Performance:

Input Voltage	120 V
Warranty	30 year limited warranty
Labels	UL-CUL Dry location listed

P2521-09CH

#### Images:



#### **Dimensions:**

Diameter: 52" Height: 14-5/8" ctc 11-9/16"

