

# AIRPRO

Ceiling downrod or close-to-ceiling mounted • Dry location listed

## Description:

Enrich any room with the ideal signature look you've been searching for. The AirPro Signature ceiling fan offers great performance and value with a powerful, 3-speed motor that can be reversed to provide year-round comfort. Includes innovative canopy system that can be installed on vaulted ceilings up to 12:12 pitch; additionally, the fan can be installed with no downrod to accommodate lower ceilings. Can be used to comply with California Title 20.

## Specifications:

- Brushed Nickel (-09) (Plated)
- Steel construction, aluminum or zinc blade arms
- 52" AirPro Collection Signature ceiling fan features five reversible blades
- Reversible Classic Walnut/Dark Walnut blades
- AirPro Collection Signature ceiling fan with Brushed Nickel finish
- Pull chain is chrome with walnut fob
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- AirPro Collection Signature ceiling fan adds form and function - by providing increased air circulation in rooms
- Features Transitional design styling
- Powerful and reversible 3-speed motor control
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- Compatible with universal light kits
- UL/CUL dry location listed
- Dual ceiling mounting on downrod, or close to ceiling
- A 3/4" x 4-1/2" downrod is included. Longer accessory downrods can be ordered separately
- Standard canopy designed for sloped ceilings up to 45 degrees (12:12 ceiling pitch)
- Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 4306 cfm, Energy consumption- 65 watts (excluding lights), Airflow efficiency- 66 cfm/watt
- 30 year limited warranty
- CanopyMounting plate for outlet box included
- 80" of wire supplied
- Classic Walnut/Dark Walnut reversible blades, plywood construction
- Chrome pull chain with Solid Wood Oak fob
- 12 degree blade pitch
- Dual-mount for downrod or close-to-ceiling installation
- Three speed control, manual reverse control
- Airflow: 4306 CFM\*
- Energy consumption: 65 watts (excluding lights)\*
- Airflow efficiency: 66 cfm/watt\*
- \* Fan on a downrod

## Performance:

Input Voltage	120 V
Warranty	30 year limited warranty
Labels	UL-CUL Dry location listed

## P2521-09WA

## Images:



## Dimensions:

Diameter: 52"  
 Height: 14-5/8"  
 ctc  
 11-9/16"

## ENERGYGUIDE

Estimated  
Yearly Energy Cost

# \$11

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 39 Watts

**Airflow**

# 3,094

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 78 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy