

AIRPRO

Ceiling downrod mounted • Dry location listed

Description:

52" Signature five-blade ceiling fan with reversible White/Natural Cherry blades, Brushed Nickel finish, and 30 year limited warranty. Powerful AirPro motor features 3-speed control that can also be reversed to provide year-round comfort. Standard canopy is designed for sloped ceilings with 12:12 pitch and a 3/4"x 4-1/2" downrod is included. Can be used to comply with California Title 20.

Specifications:

- Brushed Nickel (-09) (Plated)
- Steel construction, aluminum or zinc blade arms
- 52" AirPro ceiling fan features five reversible blades
- Reversible White/Natural Cherry blades
- AirPro ceiling fan with Brushed Nickel finish
- Pull chain is chrome with white fob
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- AirPro ceiling fan adds form and function - by providing increased air circulation in rooms
- Features Transitional design styling
- Powerful and reversible 3-speed motor
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- Compatible with universal light kits
- UL/CUL dry location listed
- Dual ceiling mounting on downrod, or close to ceiling
- A 3/4" x 4-1/2" downrod is included. Longer accessory downrods can be ordered separately
- Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 4306 cfm, Energy consumption- 65 watts (excluding lights)
- Airflow efficiency- 66 cfm/watt
- 30 year limited warranty.
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting hardware for outlet box included
- 80" of wire supplied
- White/Natural Cherry reversible blades, plywood construction
- Chrome pull chain with White fob
- 12 degree blade pitch
- Dual-mount for downrod or close-to-ceiling installation
- Three speed control, manual reverse control
- Airflow: 4306 CFM*
- Energy consumption: 65 watts (excluding lights)*
- Airflow efficiency: 66 cfm/watt*
- * Fan on a downrod

Performance:

Input Voltage	120 V
Warranty	30 year limited warranty
Labels	UL-CUL Dry location listed

P2521-09

Images:



Dimensions:

Diameter: 52"
 Height: 14-5/8"
 ctc
 11-9/16"

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$11

\$3
|
|
\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 39 Watts

Airflow

3,094

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 78 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy