

Project.		
Fixture Type:		
Location:		
Contact:		

# **AIRPRO**

Ceiling downrod mounted • Dry location listed

## **Description:**

52" Signature five-blade fan with reversible Medium Cherry/Classic Walnut blades, Antique Bronze finish, and 30 year limited warranty. Powerful AirPro motor features 3-speed control that can also be reversed to provide year-round comfort. Standard canopy is designed for sloped ceilings with 12:12 pitch and a 3/4"x 4-1/2" downrod is included. Can be used to comply with California Title 20.

## P2521-20

#### **Images:**

## Specifications:

- · Antique Bronze (-20) (Painted)
- · Steel construction, aluminum or zinc blade arms
- 52" AirPro Collection Signature ceiling fan features five reversible blades
- · Reversible Classic Walnut/Medium Cherry blades
- AirPro Collection Signature ceiling fan with Antique Bronze finish
- · Pull chain is antique brass with cherry fob
- · Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- AirPro Collection Signature ceiling fan adds form and function by providing increased air circulation in rooms
- · Features Transitional design styling
- · Powerful and reversible 3-speed motor control
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- · Compatible with universal light kits
- · UL/CUL dry location listed
- · Dual ceiling mounting on downrod, or close to ceiling
- A 3/4" x 4-1/2" downrod is included. Longer accessory downrods can be ordered separately
- Standard canopy designed for sloped ceilings up to 45 degrees (12:12 ceiling pitch)
- Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 4306 cfm, Energy consumption- 65 watts (excluding lights), Airflow efficiency- 66 cfm/watt
- · 30 year limited warranty.
- · Canopy covers a standard 4" octagonal recessed outlet box
- Mounting hardware for outlet box included
- 80" of wire supplied
- · Medium Cherry/Classic Walnut reversible blades, plywood construction
- · Antique Brass pull chain with Walnut fob
- 12 degree blade pitch
- Dual-mount for downrod or close-to-ceiling installation
- · Three speed control, manual reverse control
- · Airflow: 4306 CFM\*
- Energy consumtion: 65 watts (excluding lights)\*
- · Airflow efficiency: 66 cfm/watt\*
- \* Fan on a downrod



#### **Dimensions:**

Diameter: 52" Height: 14-5/8" ctc 11-9/16"

### Performance:

Input Voltage	120 V
Warranty	30 year limited warranty
Labels	UL-CUL Dry location listed

