

Project:

Fixture Type:

Location:

Contact:

AIRPRO

Ceiling downrod mounted • Dry location listed

Description:

Images:

52" Signature five-blade fan with reversible Medium Oak/Cherry blades, Antique Nickel finish, and 30 year limited warranty. Powerful AirPro motor features 3-speed control that can also be reversed to provide year-round comfort. Standard canopy is designed for sloped ceilings with 12:12 pitch and a 3/4"x 4-1/2" downrod is included. Can be used to comply with California Title 20.

Specifications:

- Antique Nickel (-81) (Plated)
- · Steel construction, aluminum or zinc blade arms
- 52" AirPro Collection Signature ceiling fan features five reversible blades
- Reversible Medium Oak/Cherry blades
- · AirPro Collection Signature ceiling fan with Antique Nickel finish
- Pull chain is antique brass with black fob
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- AirPro Collection Signature ceiling fan adds form and function by providing increased air circulation in rooms
- Features Transitional design styling
- · Powerful and reversible 3-speed motor control
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- Compatible with universal light kits
- UL/CUL dry location listed
- · Dual ceiling mounting on downrod, or close to ceiling
- A 3/4- x 4-1/2- downrod is included. Longer accessory downrods can be ordered separately
- Standard canopy designed for sloped ceilings up to 45 degrees (12:12 ceiling pitch)
- · Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 4306 cfm, Energy consumption- 65 watts (excluding lights), Airflow efficiency- 66 cfm/watt
- 30 year limited warranty.
- · Canopy covers a standard 4" octagonal recessed outlet box
- Mounting hardware for outlet box included
- 80" of wire supplied
- · Medium Oak/Cherry reversible blades, plywood construction
- Antique Brass pull chain with Walnut fob
- 12 degree blade pitch
- Dual-mount for downrod or close-to-ceiling installation
- Three speed control, manual reverse control
- Airflow: 4306 CFM*
- Energy consumtion: 65 watts (excluding lights)*
- Airflow efficiency: 66 cfm/watt*
- * Fan on a downrod

Performance:

Input Voltage	120 V
Warranty	30 year limited warranty
Labels	UL-CUL Dry location listed



P2521-81

Dimensions:

Diameter: 52" Height: 14-5/8" ctc 11-9/16"

