
AirPro Hugger


Ceiling Fans



			Туре				
					-09	-	-30
			P25	24			
	Finish/Blades						
Catalog	Brushed Nickel	White	Dimensions (Inches)				
No.			 Α	В			
P2524	-09	-30	42	8-5/1	6		
	Cherry/Natural Cherry	White					
	blades	blades					
	<u> </u>						
			\frown				
	B						
	Ļ				_		
				-			



Ń



Fan mounted as close-to-ceiling.

Specifications:

General

Indoor

- 15 year limited warranty
- Plated Brushed Nickel (-09) finish
- Painted White (-30) finish
- Compatible with universal light kits.
- Hugger style housing

Blades

- Four blades
- 11 degree pitch
- MDF blade material

Motor

- Three speed control; manual reverse control
- 153mm dia. x 10mm high

ENERGY INFORMATION AT HIGH SPEED

AIRFLOW:	2056 CFM cubic feet per minute
ELECTRICITY USE:	46 watts (excludes lights)
AIRFLOW EFFICIENC	CY: 45 cubic feet per minute per watt

Mounting

- Ceiling flush mount
- Unit covers a standard 4" hexagonal recessed outlet box Note: An outlet box assembly designed for fan installation is required (not included)
- Mounting hardware for outlet box included

Electrical

- Pre-wired
- Hugger fan cannot be operated with a remote control. Use P2613-30, P2619-30 pr P2630-30 for speed/light control.
- 1/8" IP accessory adapter

Labeling

• UL Dry location listed

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607