

TREVINA

Ceiling downrod or close-to-ceiling mounted • Dry location listed

Description:

52" Trevina fan with light kit, 3 blades, and 3-speed reversible motor with reverse function to provide year-round comfort. Coolly modern, the Trevina ceiling fan features a sleek Antique Bronze finish and Medium Cherry / Classic Walnut reversible blades. Can be installed on vaulted ceilings up to 30 degree. The light kit contains etched opal glass. Can be used to comply with California Title 20.

Specifications:

- Antique Bronze (-20) (Painted)
- Steel construction, aluminum or zinc blade arms
- Etched Opal glass diffuser
- 52" Trevina fan features three reversible fan blades
- Reversible Medium Cherry/Classic Walnut blades with Antique Bronze finish
- This fan does not include a switch. It is compatible with a remote control or wall switch (Control must be ordered separately)
- 3-speed reversible motor with reverse function to provide year-round comfort
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- Trevina ceiling fan adds form and function - by providing increased air circulation in rooms
- Features Modern design styling
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- The light kit contains etched opal glass and utilizes 2 medium base 13W CFL lamps(Included)
- UL-CUL dry location listed
- Ceiling mounting on downrod
- A 3/4"x 4 1/2" downrod is included. Longer accessory downrods can be ordered separately
- Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 4742 cfm, Energy consumption- 64 watts (excluding lights), Airflow efficiency- 79 cfm/watt
- Limited Lifetime warranty.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 80" of wire supplied
- Medium Cherry/Classic Walnut reversible blades, plywood construction
- 12 degree blade pitch
- Dual-mount for downrod or close-to-ceiling installation
- Three speed control, manual reverse control
- Airflow: 4742 CFM*
- Energy consumption: 64 watts (excluding lights)*
- Airflow efficiency: 79 cfm/watt*
- * Fan on a downrod

Performance:

Number of Lamps	2
Input Power	60w
Input Voltage	120 V
Warranty	Limited Lifetime warranty
Labels	UL Dry location listed

P2538-20

Images:



Dimensions:

Diameter: 52"
Height: 15-3/4"

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$11

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
• **Your cost depends on rates and use**
• Energy Use: 39 Watts

Airflow

3,187

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
• Airflow Efficiency: 81 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy