

roject:	
xture Type:	
ocation:	
ontact:	

HARRANVALE

Ceiling mounted • Dry location listed



Description:

This five-blade 54" Harranvale ceiling fan features an LED light, offering both form and function with energy- and cost-savings benefits. A white opal glass shade features a 17W, dimmable 3000K LED module. A remote with batteries is included - and controls full range dimming and fan speed capabilities. The Harranvale features a design that incorporates mixed metal design details that is very popular in today's home decor. Featuring reversible blades in a Graphite finish with Brushed Nickel accents. Can be used to comply with California Title 20. Can be used to comply with 2016 Title 24 JA8.

Specifications:

- · Graphite (-143) (painted)
- · Steel construction
- · White Opal glass diffuser
- · Harranvale ceiling fan with Graphite finish and Brushed Nickel accents
- · Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- The light kit contains a white opal glass shade and is comprised of a 17W dimmable 3000K LED module, offering 1500 lumens, 90+ CRI
- A remote with batteries is included and controls full range dimming and fan speed capabilities
- · Harranvale Collection ceiling fan adds form and function by providing increased air circulation in rooms
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- A 3/4" x 6" downrod is included. Longer accessory downrods can be ordered separately.
- · Can be used to comply with California Title 20.
- · Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- 80" of wire supplied
- · Graphite/American Walnut reversible blades, plywood construction
- · 12 degree blade pitch
- · Full Function Remote Included
- · Three speed control, manual reverse control
- · Meets California Title 24 JA8-2016
- · Airflow: 5121 CFM*
- Energy consumtion: 66 watts (excluding lights)*
- Airflow efficiency: 78 cfm/watt*
- * Fan on a downrod

P2540-14330K

Images:




Dimensions:

Diameter: 54" Height: 15-1/2"

Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1500/88.2 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	(L70/TM-21)
EMI/RFI	FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	Limited Lifetime warranty
Labels	UL Dry location listed
-	Meets California Title 24 JA8-2016





HARRANVALE

Ceiling mounted • Dry location listed PROGRESS LED

P2540-14330K

Dimming Notes:

P2540 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

"Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton - AWRMG-EAW"

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.