

SOAR

 Ceiling mounted • Dry location listed **PROGRESS LED**

Description:

With a white opal shatterproof shade and a 17W dimmable LED module, the 54" Soar ceiling fan offers energy- and cost-savings benefits for a variety of living spaces. The four-blade fan comes with a remote control and is available in a Brushed Nickel finish. LED source features a 3000K color temperature. Can be used to comply with California Title 20. Can be used to comply with 2016 Title 24 JA8.

Specifications:

- Brushed Nickel (-09) (plated)
- Steel construction
- White Opal plastic lens
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- The light kit contains a white opal shatterproof shade and is comprised of a 17W dimmable 3000K LED module, offering 1500 lumens, 90+ CRI
- A remote with batteries is included - and controls full range dimming and fan speed capabilities
- Soar ceiling fan adds form and function - by providing increased air circulation in rooms
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- A 3/4" x 6" downrod is included. Longer accessory downrods can be ordered separately
- Mounting hardware is included
- Can be used to comply with California Title 20.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- 80" of wire supplied
- Black blades, plywood construction
- 12 degree blade pitch
- Full Function Remote Included
- Three speed control, manual reverse control
- Meets California Title 24 JA8-2016
- Airflow: 4814 CFM*
- Energy consumption: 65 watts (excluding lights)*
- Airflow efficiency: 74 cfm/watt*
- * Fan on a downrod

Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1500/88.2 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	(L70/TM-21)
EMI/RFI	FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	Limited Lifetime warranty
Labels	UL Dry location listed Meets California Title 24 JA8-2016

P2542-0930K

Images:



Dimensions:

Diameter: 54"
Height: 14-1/2"

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$11

Cost Range of Similar Models (19" – 84")

\$3

\$34

• Based on 12 cents per kWh and 6.4 hours use per day
• **Your cost depends on rates and use**
• Energy Use: 41 Watts

Airflow

3,384

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
• Airflow Efficiency: 83 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

P2542-0930K

Dimming Notes:

P2542 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

"Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton - AWRMG-EAW"

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.