

ELLWOOD

Ceiling mounted • Dry location listed

Description:

A picture of modern design, the functional minimalism of the Ellwood 68" ceiling fan is a product of advanced design. Five long and graceful blades made of carved wood move air with remarkable efficiency. A remote with batteries is included – and controls full range dimming and fan speed capabilities.

Specifications:

- Antique Bronze (-20) (painted)
- Steel construction
- 68" 5 Blade Fan
- Oversized, textured die cast hanger ball reduces noise and wobble vibrations
- Mounting hardware is included
- Canopy covers a standard 4" octagonal recessed outlet box
- 80" of wire supplied
- Walnut blades, carved wood construction
- 17 degree blade pitch
- Full Function Remote Included
- A 3/4" x 8" downrod is included. Longer accessory downrods can be ordered separately. Three speed control
- Airflow: 7587 CFM*
- Energy consumption: 90 watts (excluding lights)*
- Airflow efficiency: 84 cfm/watt*
- * Fan on a downrod

Performance:

Input Voltage	120 V
Warranty	Limited Lifetime warranty
Labels	UL Dry location listed

P2546-20

Images:



Dimensions:

Diameter: 68"

Height: 15.7"

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$18

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 63 Watts

Airflow

5,834

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 92 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy