

Project:

Fixture Type:

Location:

Contact:

60" Gaze Fan

Ceiling mounted • Dry location listed PROGRESS LED

Description:

Images:


Three-blade 60 inch Gaze ceiling fan features an LED light source, offering both form and function with energy- and cost-savings benefits. An opal white shade contains an 18W dimmable, 3000K LED module. Full range dimming and remote control with batteries is included. Reversible blades in cherry and silver are included in a Brushed Nickel finish.


Specifications:

- · Brushed Nickel (-09) (plated)
- Steel Construction
- Frosted lens
- Three-blade 60" Gaze ceiling fan features an LED light source, offering both form and function with energy- and cost-savings benefits
- Gaze ceiling fan features reversible Silver/Cherry blades with a Brushed Nickel finish
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
 The light kit contains a white opal shatterproof shade and is comprised of a 18W dimmable 3000K
- LED module, offering 1400 lumens (source), 90+ CRI
- A remote with batteries is included and controls full range dimming and fan speed capabilities
- + Gaze features three speed control, manual reverse control
- Oversized ceiling fan ideal for use in spacious areas, such as large great rooms, living rooms, bedrooms and bonus rooms
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- · Suitable for Modern or Urban Industrial design styles
- A 3/4" x 6" downrod is included. Longer accessory downrods can be ordered separately
- Mounting hardware is included
- · Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 5902 cfm, Energy consumption- 75 watts (excluding lights), Airflow efficiency- 79 cfm/watt
- · Limited Lifetime Warranty.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting bracket for outlet box included
- 80" of wire supplied
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	18w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1400/77.8 (LM-82)
CCT	3000 K
CRI	90+
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-10 °C
Max. Operating Temp	30 °C
Warranty	Limited Lifetime warranty
Labels	UL Dry location listed
	Meets California Title 24 JA8-2016







P2554-0930K

Dimensions:

Diameter: 60" Height: 13-1/8"



60" Gaze Fan

Ceiling mounted • Dry location listed PROGRESS LED

P2554-0930K

Dimming Notes:

P2554 is designed to be compatible with many TRIAC/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron - NTEVL-300	
Lutron - DVELV-300P	
Lutron-DVCL-253P	
Lutron - Caseta Wireless	
IDevices - IDEV009	
Leviton – 6672	
Leviton – 6674	
Lutron - AYCL-153P	
Lutron - TGCL-153-PH-WH	
Lutron - AYLV-600P	
Lutron - MAELV-601	
Leviton -AWSMT-EAW	
Lutron - N-600	

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.