

| roject:      |  |  |
|--------------|--|--|
| ixture Type: |  |  |
| ocation:     |  |  |
| Contact:     |  |  |

## 52" Trevina Fan

Ceiling mounted • Dry location listed PROGRESS LED

## **Description:**

The 52 inch Trevina II features three blades available in Antique Bronze finish. Coolly modern, the Trevina II ceiling fan offers both form and function with an energy efficient 17W LED source with a 3000K-color temperature. Features a wall control switch. Can be used to comply with California Title 20.

### **Specifications:**

- · White (-30) (painted)
- · Steel construction
- · Etched Opal glass bowl
- 52" Trevina ceiling fan features an LED light source, offering both form and function with energyand cost-savings benefits
- The light kit contains a etched opal glass shade and is comprised of a 17W dimmable 3000K LED module, offering 1400 lumens (source), 90+ CRI
- · Trevina fan features three reversible Natural Cherry/White fan blades and White finish
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- · Features Modern and Transitional design styling
- · Ceiling mounting on downrod
- Includes easy to assemble canopy system that can be installed on vaulted ceilings up to 30° slope
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- · Includes a wall control switch
- · Three speed control, manual reverse control
- Trevina ceiling fan adds form and function by providing increased air circulation in rooms
- A 3/4" x 4-1/2" downrod is included. Longer accessory downrods can be ordered separately
- · Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 4742 cfm, Energy consumption- 64 watts (excluding lights), Airflow efficiency 74 cfm/watt
- Limited lifetime warranty
- · Dimmable to 10% brightness (See Dimming Notes)
- · Canopy covers a standard 4" octagonal recessed outlet box
- · Mounting plate for outlet box included
- 80" of wire supplied
- Meets California Title 24 JA8-2016

# P2556-3030K

### **Images:**



#### **Dimensions:**

Diameter: 52" Height: 15-3/4"

Glass

Width: 9-3/16" Height: 2-7/8"

#### **Performance:**

| Number of Modules   | 1                                  |  |
|---------------------|------------------------------------|--|
| Input Power         | 17w                                |  |
| Input Voltage       | 120 V                              |  |
| Input Frequency     | 60 Hz                              |  |
| Lumens/LPW (Source) | 1400/82 (LM-82)                    |  |
| CCT                 | 3000 K                             |  |
| CRI                 | 90 CRI                             |  |
| Life (hours)        | 50,000 (L70/TM-21)                 |  |
| FCC                 | FCC Title 47, Part 15, Class B     |  |
| Min. Start Temp     | -10 °C                             |  |
| Max. Operating Temp | 30 °C                              |  |
| Warranty            | Limited Lifetime warranty          |  |
| Labels              | ULus Dry location listed           |  |
|                     | Meets California Title 24 JA8-2016 |  |
|                     |                                    |  |

