

Project:			
Fixture Type:			
Location:			

Caleb

Ceiling downrod Mounted • Dry Location Listed

Contact:

Description:

Caleb Collection 68-Inch 5-Blade Antique Bronze AC Motor Transitional Ceiling Fan

Specifications:

- Canopy covers a standard 4" recessed outlet box: 5.875 in W., 2.375 in ht., 5.875 in depth
- · Mounting Bracket
- · 80 in of wire supplied

Performance:

Input Voltage	120 V
Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime warranty
Labels	UL Dry Location Listed
	AC motor







Dimensions:

Length: 68 in Diameter: 68 in Height: 18 in

