



DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_



# P2560-20

## Caleb

Beautiful and expansive in design, the 68" Caleb ceiling fan is ideal for use in large spaces. Bent Carved Wood blades are paired with either finished in an Antique Bronze finish. Caleb features a dual mount system and is compatible with universal light kits. A full function remote control with batteries is included.

- 68" Caleb ceiling fan features a spacious design with bent five carved wood blades
- Caleb ceiling fan features Walnut blades with an Antique Bronze finish
- Five long and graceful blades made of carved wood move air with remarkable efficiency
- Beautiful and expansive in design, the 68" Caleb ceiling fan is ideal for use in large spaces – such as great rooms, bedrooms and other living areas
- Caleb features a dual mount system and is compatible with universal light kits
- A full function remote control with batteries is included
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- UL dry location listed
- Reversible motor for year round comfort allows you to choose either a down draft (summer) or an up draft (winter)
- Add a P2631-30 wall control for added convenience
- High Speed Energy Information: Airflow— 7045 cfm, Energy consumption— 86 watts (excluding lights), Airflow efficiency— 82 cfm/watt
- Limited Lifetime Warranty

**Diameter: 68"**  
**Height: 18"**

**Category:** Ceiling Fans

**Finish:** Antique Bronze (Painted)

**Construction:** Steel construction

ENERGYGUIDE	
<b>Estimated</b> <b>Yearly Energy Cost</b> <b>\$17</b>	<b>Airflow</b> <b>5,508</b> Cubic Feet Per Minute
	<ul style="list-style-type: none"> <li>• The higher the airflow, the more air the fan will move</li> <li>• Airflow Efficiency: 91 Cubic Feet Per Minute Per Watt</li> </ul>
<small>Cost Range of Similar Models (19" – 84")</small> <small>• Based on 12 cents per kWh and 6.4 hours use per day</small> <small>• Your cost depends on rates and use</small> <small>• Energy Use: 61 Watts</small>	
<small>All estimates based on typical use, excluding lights</small>	
<small>ftc.gov/energy</small>	

MOUNTING	ELECTRICAL	ADDITIONAL INFORMATION
Ceiling mounted  Mounting strap for outlet box included  Canopy covers a standard 4" octagonal recessed outlet box  6.5" W., 2.5" ht., 6.5" depth	Pre-wired  80" of wire supplied  120 V	UL Dry location listed  Limited Lifetime warranty  with n/a fob