

Project:		
Fixture Type:		
Location:		
Contact:		

# **LAKEHURST**

Ceiling mounted · Wet location listed

### **Description:**

This five-blade 60" Lakehurst ceiling fan features an all weather wet location rating (ABS) to accommodate a variety of interior and exterior locations. Compatible with universal light kits, Lakehurst features a dual mount system and a three-speed pull chain fan switch. ABS blades. Fan has three finish options available: Antique Bronze, White and Forged Black. Can be used to comply with California Title 20.

# P2562-20

#### Images:

## **Specifications:**

- · Antique Bronze (-20) (Painted)
- · Steel construction
- 60" Lakehurst indoor/outdoor ceiling fan features a spacious design with five ABS blades
- · Lakehurst ceiling fan features Walnut blades with an Antique Bronze finish
- Beautiful and expansive in design, the 60" Lakehurst ceiling fan is ideal for use in large indoor and outdoor spaces
- · ABS all weather blades are included for maintenance free operation inside or out
- · Compatible with universal light kits
- · Includes a three speed pull chain fan switch for easy speed or on/off adjustments
- Lakehurst features a dual mount system to offer greater flexibility when installing the fan can be installed on a flat or sloped ceiling
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- Features an all weather wet location rating to accommodate a variety of interior and exterior locations.
- Reversible motor for year round comfort allows you to choose either a down draft (summer) or an up draft (winter)
- · Add a P2630-30 wall control or P2614-30 remote control for added convenience
- · Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 6440 cfm, Energy consumption- 71 watts (excluding lights), Airflow efficiency- 91 cfm/watt
- · Limited Lifetime Warranty.
- · Canopy covers a standard 4" octagonal recessed outlet box
- · Mounting strap for outlet box included
- · 80" of wire supplied
- · Walnut blades, plywood construction
- · Brass pull chain with Walnut fob
- · 13.5 degree blade pitch



#### **Dimensions:**

Diameter: 60" Height: 15-3/4"

#### Performance:

Input Voltage	120 V
Input Frequency	60 Hz
EMI/RFI	Title 20
Warranty	Limited Lifetime warranty
Labels	UL Wet location listed

