

Project:		
Fixture Type:		
Location:		
Contact:		

MONTAGUE

Ceiling mounted • Wet location listed



Description:

This five-blade 60" Montague ceiling fan features an all weather wet location rating (ABS) to accommodate a variety of interior and exterior locations. The white opal glass shade contains a 17W dimmable, 3000K LED module, offering both form and function with energy- and cost-savings benefits. A remote with batteries is included. The Montague features a dual mount system to offer greater flexibility when installing. ABS blades are available in with three finish options: Antique Bronze, White and Forged Black. Can be used to comply with California Title 20.

Specifications:

- · Antique Bronze (-20) (Painted)
- · Steel construction
- White opal glass Bowl
- The white opal glass shade contains a 17W dimmable, 3000K LED module, 90+ CRI and 1400 lumens - offering both form and function with energy- and cost-savings benefits
- Beautiful and expansive in design, the 60" Montague ceiling fan is ideal for use in large indoor and outdoor spaces
- ABS all weather blades are included for maintenance free operation inside or out
- A hand held remote control with fan speed control and full range light dimming is included and comes with a convenient wall bracket for storage
- Montague features a dual mount system to offer greater flexibility when installing the fan can be installed on a flat or sloped ceiling
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- Features an all weather wet location rating to accommodate a variety of interior and exterior locations
- Reversible motor for year round comfort allows you to choose either a down draft (summer) or an up draft (winter)
- · Add a P2630-30 wall control for added convenience
- · Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 6693 cfm, Energy consumption- 75 watts (excluding lights), Airflow efficiency- 89 cfm/watt
- · Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- · 80" of wire supplied
- · Walnut blades, plastic construction
- 13 degree blade pitch
- Full Function Remote Included
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	18w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1386/77 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	46,000 (L70/TM-21)
EMI/RFI	Title 20
Min. Start Temp	-10 °C
Max. Operating Temp	40 °C
Warranty	Limited Lifetime warranty
Labels UL Wet location listed	
-	Meets California Title 24 JA8-2016


P2564-2030K

Images:



Dimensions:

Diameter: 60" Height: 17-5/8"





MONTAGUE

Ceiling mounted • Wet location listed PROGRESS LED

P2564-2030K

Dimming Notes:

P2564 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

"Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton – 6672

Leviton - 6674

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton - AWRMG-EAW"

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.