

#### Project:

Fixture Type:

Location:

Contact:

Ceiling mounted • Dry location listed PROGRESS LED

# KUDOS

## **Description:**

This five-blade 52" Kudos ceiling fan features a clear Fresnel glass shade. Includes a remote control with batteries. The Kudos features a dual mount system to offer greater flexibility when installing. The 17W dimmable, 3000K LED module provides energy- and cost-savings benefits to the home-owner. Can be used to comply with California Title 20.

#### **Specifications:**

- · Antique Bronze (-20) (Painted)
- Steel construction
- Clear fresnel glass Diffuser
- 52" Kudos ceiling fan features five blades and a clear Fresnel glass shade
- Reversible Walnut/Cherry blades and an Antique Bronze finish
- Includes a remote control with batteries that offers fan speed control and full range light dimming - comes with a convenient wall bracket for storage
- The Kudos features a dual mount system to offer greater flexibility when installing
- The 17W dimmable, 3000K LED module features 90CRI and 1400 lumens
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- Features roots in an industrial style and is suitable for transitional design styling
- Reversible motor for year round comfort allows you to choose either a down draft (summer) or an up draft (winter)
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- UL Dry location listed
- Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 5160 cfm, Energy consumption- 60 watts (excluding lights), Airflow efficiency- 86 cfm/watt
- Limited Lifetime Warranty.
- · Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 80" of wire supplied
- · Walnut/Cherry blades, plywood construction
- 13 degree blade pitch
- Full Function Remote Included
- Meets California Title 24 JA8-2016

## Performance:

Number of Modules	1
Input Power	18w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1386/77 (LM-79)
ССТ	3000 К
CRI	90 CRI
Life (hours)	46,000 (L70/TM-21)
EMI/RFI	Title 20
Min. Start Temp	-10 °C
Max. Operating Temp	40 °C
Warranty	Limited Lifetime warranty
Labels	UL Dry location listed
	Meets California Title 24 JA8-2016


# P2568-2030K

#### Images:



#### **Dimensions:**

Diameter: 52" Height: 17-5/8"



For more information visit our website: www.progresslighting.com



# KUDOS

Ceiling mounted • Dry location listed PROGRESS LED

# P2568-2030K

### **Dimming Notes:**

P2568 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls**

"Lutron - NTEVL-300
Lutron - DVELV-300P
Lutron - Caseta Wireless
Leviton – 6672
Leviton – 6674
Lutron - AYCL-153P
Lutron - AYLV-600P
Lutron - MAELV-601
Leviton - AWRMG-EAW"

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.