

# VOX

 Ceiling mounted • Dry location listed **PROGRESS LED**

## Description:

Five-blade 52 inch Vox Hugger ceiling fan features medium cherry blades and a Brushed Nickel finish. The LED light source offers both form and function with energy- and cost-savings benefits. A shatterproof, white opal shade contains a 17W dimmable, 3000K LED module. A remote control with batteries is included. The fan mounts close to the ceiling.

## Specifications:

- Brushed Nickel (-09) (plated)
- Steel Construction
- Etched opal glass Diffuser
- 52" Vox hugger ceiling fan features an LED light source, offering both form and function with energy- and cost-savings benefit
- A shatterproof, white opal shade contains a 17W dimmable, 3000K LED module with 90CRI and 1400 lumens (source)
- Indoor ceiling fan ideal for rooms with low ceiling heights
- Features Medium Cherry blades and a Brushed Nickel finish
- Vox hugger fan mounts close to the ceiling only
- A full function hand held remote control with fan speed control, including reverse, and full range light dimming is included and comes with a convenient wall bracket for storage
- Features modern styling for contemporary living spaces
- Reversible motor for year round comfort allows you to choose either a down drafts (summer) or an up draft (winter)
- Remote control may be replaced by a P2631-30 wall control
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- UL Dry location listed and rated for indoor use
- Can be used to comply with California Title 20.
- Limited Lifetime Warranty.
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 80" of wire supplied
- Medium Cherry blades, plywood construction
- 12 degree blade pitch
- Three speed control, manual reverse control Speed, Remote Control Reverse
- Meets California Title 24 JA8-2016
- Airflow: 4276 CFM
- Energy consumption: 62 watts (excluding lights)
- Airflow efficiency: 68 cfm/watt

## Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1386/77 (LM-82)/
CCT	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
EMI/RFI	Title 20
Min. Start Temp	-10 °C
Max. Operating Temp	40 °C
Warranty	Limited Lifetime warranty
Labels	UL Dry location listed
	Meets California Title 24 JA8-2016

## P2572-0930K

## Images:



## Dimensions:

Diameter: 52"  
Height: 11-5/8"

Diffuser  
Width: 9-9/16"  
Height: 2-3/8"

# ENERGYGUIDE

Estimated  
Yearly Energy Cost

## \$11

\$3
\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 40 Watts

Airflow

## 3,040

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 76 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

**P2572-0930K****Dimming Notes:**

---

P2572 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

**Dimming Controls**

---

Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton - AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.