

#### Project:

Fixture Type:

Location:

Contact:

Ceiling mounted • Dry location listed PROGRESS LED

# TEMPT

## **Description:**

This five-blade 52" Tempt ceiling fan features a clear glass shade. A remote with batteries is included. Tempt features a dual mount system to offer greater flexibility when installing. The 17W dimmable, 3000K LED module provides energy- and cost-savings benefits to the homeowner. Can be used to comply with California Title 20.

### **Specifications:**

- · Polished Chrome (-15) (Plated)
- Steel construction
- Clear double cut prismatic glass Bowl
- The light kit contains a clear double cut prismatic glass shade and contains a 17W dimmable 3000K LED module with 90CRI and 1400 lumens
- Features reversible Medium Cherry/Black blades and a Polished Chrome finish
- A hand held remote control with fan speed control and full range light dimming is included and comes with a convenient wall bracket for storage
- The five-blade Tempt fan features a dual mount system to offer greater flexibility when installing. The fan can be installed on a flat or sloped ceiling
- · Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- Ideal for Transitional interiors
- · Reversible motor for year round comfort allows you to choose either a down draft (summer) or an up draft (winter)
- · As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges
- from 226- to 400-square feet
- UL dry location listed for indoor use
- A 3/4" x 4-1/2" downrod is included. Longer accessory downrods can be ordered separately
- Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 4314 cfm, Energy consumption- 62 watts (excluding lights), Airflow efficiency- 78 cfm/watt
- · Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 80" of wire supplied
- Medium Cherry/Black reversible blades, plywood construction

For more information visit our website: www.progresslighting.com

- 12 degree blade pitch
- Full Function Remote Included
- · Meets California Title 24 JA8-2016

## Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1386/77 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
EMI/RFI	Title 20
Min. Start Temp	-10 °C
Max. Operating Temp	40 °C
Warranty	Limited Lifetime warranty
Labels	UL Dry location listed
-	Meets California Title 24 JA8-2016


# P2578-1530K

#### Images:



#### **Dimensions:**

Diameter: 52" Height: 14-3/4"





# TEMPT

Ceiling mounted • Dry location listed PROGRESS LED

# P2578-1530K

## **Dimming Notes:**

P2578 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

# **Dimming Controls**

"Lutron - NTEVL-300
Lutron - DVELV-300P
Lutron - Caseta Wireless
Leviton – 6672
Leviton – 6674
Lutron - AYCL-153P
Lutron - AYLV-600P
Lutron - MAELV-601
Leviton - AWRMG-EAW"

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.