

BRADEN

 Ceiling mounted • Dry location listed 

Description:

This Braden 56", three-blade, hugger-style ceiling fan features clean lines and a design that complements modern interiors. A shatterproof white opal glass shade contains an integrated 18W LED module, offering both form and function with energy and cost-savings benefits. Featuring a larger motor, Braden moves more air than a traditional hugger ceiling fan. A full function remote with batteries is included.

Specifications:

- Brushed Nickel (-09) (plated)
- Steel construction
- White Opal Shatterproof glass Flat Round
- 56" Braden three-blade hugger ceiling fan features an LED light source, offering both form and function with energy- and cost-savings benefit
- A white opal, shatterproof shade contains a 18W dimmable, 3000K LED module with 90CRI and 1400 lumens
- Indoor ceiling fan ideal for rooms with low ceiling heights
- Features reversible American Walnut blades and Silver blades
- Timeless Brushed Nickel finish
- Braden features a larger motor and moves more air than a traditional hugger ceiling fan
- Braden hugger fan mounts close to the ceiling only
- A Full function hand held remote control with fan speed control, reverse control and full range light dimming is included and comes with a convenient wall bracket for storage
- Features modern styling for contemporary living spaces
- Reversible motor for year round comfort allows you to choose either a down drafts (summer) or an up draft (winter)
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting Yes for outlet box included
- 80" of wire supplied
- Silver/American Walnut reversible blades, plywood construction
- 13 blade pitch
- Full function remote included
- Three speed control, manual reverse control Speed, Manual Reverse
- Airflow: 4263 CFM*
- Energy consumption: 55 watts (excluding lights)*
- Airflow efficiency: 77 cfm/watt*
- * Fan on a downrod

Performance:

Number of Modules	1
Input Power	18w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1400/77 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
Warranty	Limited Lifetime
Labels	cULus Dry location listed

P2588-0930K

Images:



Dimensions:

Diameter: 56"
Height: 9-7/8"

Glass
Width: 6"
Height: 1-5/8"

P2588-0930K

Dimming Notes:

P2588 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron-DVCL-253P

Lutron - Caseta Wireless

IDevices - IDEV009

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - TGCL-153-PH-WH

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton -AWSMT-EAW

Lutron - N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.