

Project:		
Fixture Type:		
Location:		
Contact:		

# **SHAFFER**

Ceiling mounted • Dry location listed

## **Description:**

The 56" Schaffer four-blade ceiling fan blends a streamlined design with mixed metal elements and a wire mesh housing, suitable for modern and urban industrial spaces. The Architectural Bronze ceiling comes with brushed bronze accents. A remote control with batteries is included.

### **Specifications:**

- · Architectural Bronze (-129) (plated)
- · Steel construction
- The 4-blade 56" Shaffer ceiling fan blends a streamlined design with mixed metal elements and a wire mesh housing
- · Shaffer features reversible Driftwood and Natural Cherry blades
- · Rich Architectural Bronze finish with Brushed Bronze accents
- The clean and modern design of the Shaffer is ideal for use in a variety of spaces, including great rooms, bedrooms, offices and other living areas
- · Features a dual mount system
- · A full function three-speed remote control with batteries is included
- The design is suitable for modern and urban industrial spaces
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- · Reversible Medium Cherry and Classic Walnut blades
- Canopy covers a standard 4" octagonal recessed outlet box
- · Mounting Yes for outlet box included
- · 80" of wire supplied
- · Driftwood/Natural Cherry reversible blades, plywood construction
- 13.5 blade pitch
- · Full function remote included
- · Three speed control, manual reverse control Speed, Manual Reverse
- · Airflow: 6144 CFM\*
- Energy consumtion: 67 watts (excluding lights)\*
- Airflow efficiency: 91 cfm/watt\*
- \* Fan on a downrod

#### **Performance:**

Input Voltage	120 V
Input Frequency	60 Hz
Warranty	Limited Lifetime
Labels	cULus Dry location listed

P2590-129

**Images:** 



#### **Dimensions:**

Diameter: 56" Height: 16-1/4"