

Project:		
Fixture Type:		
Location:		
Contact:		

SHAFFER

Ceiling mounted • Dry location listed

Description:

The 56" Schaffer four-blade ceiling fan blends a streamlined design with mixed metal elements and a wire mesh housing, suitable for modern and urban industrial spaces. Satin White ceiling fan has galvanized accents. A remote control with batteries is included.

Specifications:

- · Satin White (-28) (painted)
- · Steel construction
- The 4-blade 56" Shaffer ceiling fan blends a streamlined design with mixed metal elements and a wire mesh housing
- · Shaffer features reversible Brushed Nickel and White blades
- · Satin White finish with Galvanized accents
- The clean and modern design of the Shaffer is ideal for use in a variety of spaces, including great rooms, bedrooms, offices and other living areas
- · Features a dual mount system
- · A full function three-speed remote control with batteries is included
- The design is suitable for modern and urban industrial spaces
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than
 accordance feet
- · Canopy covers a standard 4" octagonal recessed outlet box
- · Mounting Yes for outlet box included
- 80" of wire supplied
- · White/Silver reversible blades, plywood construction
- 13.5 blade pitch
- Full function remote included
- · Three speed control, manual reverse control Speed, Manual Reverse
- · Airflow: 6144 CFM*
- · Energy consumtion: 67 watts (excluding lights)*
- · Airflow efficiency: 91 cfm/watt*
- · * Fan on a downrod

Performance:

Input Voltage	120 V
Input Frequency	60 Hz
Warranty	Limited Lifetime
Labels	cULus Dry location listed

P2590-28

Images:



Dimensions:

Diameter: 56" Height: 16-1/4"