

ORIOLE

 Ceiling mounted • Dry location listed 

Description:

This 60" Oriole three-blade ceiling fan is the perfect addition to garages, industrial shops or commercial buildings to distribute the right amount of air and keep the space cool and comfortable. Oriole contains an integrated 18W LED module, with an optional finishing cap offering the user the choice to install with or without the light kit. A remote control is included. A blank off plate comes standard.

Specifications:

- Architectural Bronze (-129) (painted)
- Steel construction
- White Opal Plastic Flat Round
- This 60" three-blade Oriole ceiling fan distributes the right amount of air to keep the space cool and comfortable
- Rich Architectural Bronze finish with Architectural Bronze ABS blades
- This ceiling fan is the perfect addition to garages, industrial shops or commercial buildings to distribute the right amount of air and keep the space cool and comfortable.
- Features 18W white shatterproof dimmable 3000K LED module, offering 1400 lumens, 90+ CRI with an optional finishing cap offering the user the choice to install with or without the light kit
- A three-speed remote with batteries is included – and controls full range dimming and fan speed capabilities
- Manual reverse switch for year round comfort
- Ideal for Modern, Contemporary and Industrial settings
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- Dual mount canopy that accommodates flat or sloped ceilings (sloped -18.5 degrees)
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting Yes for outlet box included
- 80" of wire supplied
- Bronze blades, abs construction
- 21 blade pitch
- Full function remote included
- Three speed control, manual reverse control Speed, Manual Reverse
- Airflow: 6446 CFM*
- Energy consumption: 48 watts (excluding lights)*
- Airflow efficiency: 134 cfm/watt*
- * Fan on a downrod

Performance:

Number of Modules	1
Input Power	18w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1400/77 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
Warranty	Limited Lifetime
Labels	cULus Dry location listed

P2592-12930K

Images:



Dimensions:

Diameter: 60"
Height: 14-1/2"

Glass
Width: 7-3/4"
Height: 1-3/4"

P2592-12930K

Dimming Notes:

P2592 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron-DVCL-253P

Lutron - Caseta Wireless

IDevices - IDEV009

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - TGCL-153-PH-WH

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton -AWSMT-EAW

Lutron - N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.