

roject:	
ixture Type:	
ocation:	
ontact:	

SANFORD

Ceiling mounted • Damp location listed



Description:

Sanford delivers ultra powerful air movement and energy efficient illumination packaged in a modern design. Ideal for both interior and outdoor settings, this fan adds a contemporary style to porches, foyers, bath and vanity areas providing a wide range of applications. Sanford includes an integrated 23W LED module, offering both form and function with energy and cost-savings benefits. Remote control included.

Specifications:

- · Brushed Nickel (-09) (plated)
- · Steel construction
- · White Shatterproof Plastic
- This "fandelier" delivers ultra-powerful air movement and energy efficient illumination packaged in a modern design
- · Timeless Brushed Nickel finish with metal interior fan blades
- · Adds a contemporary style to porches, foyers, bath and vanity areas providing a wide range of applications
- · Features 23W white shatterproof dimmable 3000K LED module,
- A three-speed remote with batteries is included and controls full range dimming and fan speed capabilities
- · Manual reverse switch for year round comfort
- · Ideal for Modern, Contemporary and Industrial settings
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is 75-square feet or less
- Dual mount canopy that accommodates flat or sloped ceilings
- · Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting Yes for outlet box included
- · 80" of wire supplied
- · Brushed Nickel blades, steel construction
- 31.7 blade pitch
- Full function remote included
- · Three speed control, manual reverse control Speed, Manual Reverse
- · Airflow: 1008 CFM*
- · Energy consumtion: 37 watts (excluding lights)*
- Airflow efficiency: 27 cfm/watt*
- * Fan on a downrod

Performance:

Number of Modules	1
Input Power	23w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1990/86 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	35,000 (L70/TM-21)
Warranty	Limited Lifetime
Labels	cULus Damp location listed
Warranty	Limited Lifetime

P2594-0930K

Images:



Dimensions:

Diameter: 22-7/8" Height: 17-3/4"



SANFORD

Ceiling mounted • Damp location listed PROGRESS LED

P2594-0930K

Dimming Notes:

P2594 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron-DVCL-253P

Lutron - Caseta Wireless

IDevices - IDEV009

Leviton - 6681

Leviton - IPI06-1LZ

Leviton - 6672

Leviton - 6674

Lutron - AYCL-153P

Lutron - SCL-153P

Lutron - TGCL-153-PH-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.