

roject:		
ixture Type:		
ocation:		
ontact:		

## **EDISTO**

Ceiling mounted • Damp location listed



### **Description:**

The Edisto 54" two-blade outdoor ceiling fan combines a sleek, contemporary style with high-quality performance. A wire frame supports canvas wrapped blades that feature UV inhibitors to protect the fabric from fading in the sunlight. Three fan speeds and a reversible switch keep individuals cool in the summer and warm in the winter. A white opal glass shade contains an 18W LED module light kit, offering energy efficient and cost savings benefits.

#### **Specifications:**

- · Architectural Bronze (-129) (painted)
- Steel construction
- · White Opal Plastic Flat Round
- 54" two-blade Edisto outdoor ceiling fan combines a sleek, contemporary style with high-quality performance
- A wire frame supports Canvas wrapped blades that feature UV inhibitors to protect the fabric from fading in the sunlight
- · Warm Mushroom Canvas blades
- · Rich Architectural Bronze finish
- Refresh your indoor or covered outdoor living spaces with the crisp, clean style of the 54" Edisto fan
- The Two blade fan features an all-weather damp location rating to accommodate a variety of settings throughout the home
- White opal shatterproof shade with a 18W dimmable LED light source offers a warm 3000K-color temperature, 90 CRI and 1400 lumens
- A hand held remote control with fan speed control and full range light dimming is included and comes with a convenient wall bracket for storage
- Features modern styling for Contemporary, Mid-Century Modern living spaces
- Reversible motor for year round comfort allows you to choose either a down drafts (summer) or an up draft (winter)
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to
- A 1"x 6" downrod is included. Longer accessory downrods can be ordered separately
- Dimmable to 10% brightness (See Dimming Notes)
- · Canopy covers a standard 4" octagonal recessed outlet box
- · Mounting Yes for outlet box included
- 80" of wire supplied
- · Mushroom blades, canvas construction
- · 20 blade pitch
- · Full function remote included
- · Three speed control, manual reverse control Speed, Manual Reverse
- · Airflow: 4371 CFM\*
- Energy consumtion: 65 watts (excluding lights)\*
- · Airflow efficiency: 67 cfm/watt\*
- \* Fan on a downrod

#### **Performance:**

Number of Modules	1	
Input Power	18w	
Input Voltage	120 V	
Input Frequency	60 Hz	
Lumens/LPW	1400/77 (LM-79)	
ССТ	3000 K	
CRI	90 CRI	
Life (hours)	50,000 (L70/TM-21)	
Warranty	Limited Lifetime	
Labels	ULus Damp location listed	

## P2596-12930K

#### Images:



#### **Dimensions:**

Diameter: 54" Height: 14-7/8"

Glass

Width: 7-1/4" Height: 2"



# **EDISTO**

Ceiling mounted • Damp location listed PROGRESS LED

P2596-12930K

## **Dimming Notes:**

P2596 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls**

Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron-DVCL-253P

Lutron - Caseta Wireless

IDevices - IDEV009

Leviton - 6672

Leviton - 6674

Lutron - AYCL-153P

Lutron - TGCL-153-PH-WH

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton -AWSMT-EAW

Lutron - N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.