

Project:			
Fixture Type:			
Location:			

Olson

Ceiling Mounted • Dry Location Listed

Contact:

Description:

The 52 in Olson five-blade ceiling fan features a generously sized etched watermark glass shade and sweeping blades highlighted with metal accents. Two 9W LED lamps are JA8 compliant, offering both form and function with energy and cost-savings benefits. Olson features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light. Brushed Nickel finish.

Specifications:

- · White Opal glass Bowl
- 52" Olson Collection ceiling fan features five generously sized sweeping reversible blades
- · Reversible Medium Cherry and Classic Walnut blades
- · Timeless Brushed Nickel finish
- Features a dual mount system and a three-speed pull chain fan switch, as well as an on/ off pull chain switch to operate the light
- · Pull chain is chrome
- · Add an accessory wall or remote control for added convenience
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- $\boldsymbol{\cdot}$ Ceiling fan adds form and function by providing increased air circulation in rooms
- · Features Transitional design styling
- · Powerful and reversible 3-speed motor control
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- · Light kit features white opal glass
- Two 9W LED lamps are JA8 compliant, offering both form and function with energy and cost-savings benefits
- · UL/CUL dry location listed
- · Dual ceiling mounting on downrod, or close to ceiling
- A 3/4" x 6" downrod is included. Longer accessory downrods can be ordered separately
- · Airflow: CFM
- Energy consumption: 67 watts*
- · Airflow efficiency: 91 cfm/watt*
- · * Fan on a downrod
- · Fully dimmable with dimmable bulbs.
- Canopy covers a standard 4" recessed outlet box
- · Mounting bracket for outlet box included
- · 80 in of wire supplied

Performance:

Number of Lamps	2		
Input Power	9 W		
Input Voltage	120 V		
Input Frequency	60 Hz		
Lumens/LPW (Source)	800/88 (LM-82)		
CCT	3000 K		
CRI	90 CRI		
Life (hours)	25000 (L70/TM-21)		
Warranty	Limited Lifetime warranty		
Labels	cULus Dry Location Listed		
	Meets California Title 24 JA8-2016		
	AC motor		

P2598-09




Dimensions:

Diameter: 52 in Height: 21-3/8 in

White Opal glass Bowl

Width: 11 in Height: 5-1/8 in





Olson

Ceiling Mounted • Dry Location Listed

Dimming Notes:

P2598-09

P2598-09 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Maestro MAELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.