

Proj	ject:

Fixture Type:

Location: Contact:

Olson

Ceiling Mounted • Dry Location Listed

Description:

The 52 in Olson five-blade ceiling fan features a generously sized etched watermark glass shade and sweeping blades highlighted with metal accents. Two 9W LED lamps are JA8 compliant, offering both form and function with energy and cost-savings benefits. Olson features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light. Graphite finish.

Specifications:

- White Opal glass Bowl
- · 52" Olson Collection ceiling fan features five generously sized sweeping reversible blades
- $\boldsymbol{\cdot}\,$ Reversible Walnut and Graphite blades
- \cdot Graphite finish
- Features a dual mount system and a three-speed pull chain fan switch, as well as an on/ off pull chain switch to operate the light
- Pull chain is chrome
- Add an accessory wall or remote control for added convenience
- $\boldsymbol{\cdot}$ Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- \cdot Ceiling fan adds form and function by providing increased air circulation in rooms
- Features Transitional design styling
- + Powerful and reversible 3-speed motor control
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- · Light kit features white opal glass
- Two 9W LED lamps are JA8 compliant, offering both form and function with energy and cost-savings benefits
- UL/CUL dry location listed
- Dual ceiling mounting on downrod, or close to ceiling
- + A 3/4" x 6" downrod is included. Longer accessory downrods can be ordered separately
- Airflow: CFM*
- Energy consumption: 67 watts*
- Airflow efficiency: 91 cfm/watt*
- \star Fan on a downrod
- + Fully dimmable with dimmable bulbs.
- · Canopy covers a standard 4" recessed outlet box
- Mounting bracket for outlet box included
- 80 in of wire supplied

Performance:

Number of Lamps	2
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	800/88 (LM-82)
ССТ	3000 K
CRI	90 CRI
Life (hours)	25000 (L70/TM-21)
Warranty	Limited Lifetime warranty
Labels	cULus Dry Location Listed
	Meets California Title 24 JA8-2016
	AC motor




P2598-143

Dimensions:

Diameter: 52 in Height: 21-3/8 in

White Opal glass Bowl Width: 11 in Height: 5-1/8 in





Olson

Ceiling Mounted • Dry Location Listed

Dimming Notes:

P2598-143 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Maestro MAELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

