

Project:		
Fixture Type:		
Location:		
Contact:		

BUILDER FAN

Ceiling mounted · Dry location listed

Description:

A 52" two-light, five-blade fan with reversible blades and a beautifully crafted white etched glass bowl. Powerful AirPro motor features 3-speed control that can also be reversed to provide year-round comfort. Two medium-based LED lamps are included, offering energy efficiency and cost savings benefits for the home, while a dual mount canopy accommodates flat or sloped ceilings.

Specifications:

- · Brushed Nickel (-09) (plated)
- · Steel construction
- · White Etched Glass Bowl
- 52" ceiling fan with light kit features five reversible blades
- Reversible Cherry/Natural Cherry blades
- · Ceiling fan with timeless Brushed Nickel finish
- Features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light
- · White etched glass bowl with two medium-based LED lamps are included
- · Pull chain is chrome with a maple fob
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- Ceiling fan adds form and function by providing increased air circulation in rooms
- · Features Traditional design styling
- · Powerful and reversible 3-speed motor control
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- · Dual ceiling mounting on downrod, or close to ceiling
- A 1"x 4-1/4" downrod is included. Longer accessory downrods can be ordered separately
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting Yes for outlet box included
- · 80" of wire supplied
- · Cherry/Natural Cherry reversible blades, mdf/plywood construction
- · Chrome pull chain with Maple fob
- · Dual-mount for downrod or close-to-ceiling installation
- · Three speed control, manual reverse control Speed, Manual Reverse
- · Airflow: 3300 CFM*
- · Airflow efficiency: 82 cfm/watt*
- * Fan on a downrod

Performance:

Number of Modules	2	
Input Power	8.5w	
Input Voltage	120 V	
Input Frequency	60 Hz	
Lumens/LPW	1600/94 (LM-79) per module	
CCT	3000 K	
CRI	80 CRI	
Life (hours)	15,000 (L70/TM-21)	
Warranty	30 Year	
Labels	ULus Dry location listed	

P2599-09

Images:



Dimensions:

Diameter: 52" Height: 19-1/8"

Glass

Width: 10-3/4" Height: 4-3/8"