

Springer

Ceiling fan light kit Mounted • Dry Location Listed

Description:

Springer Collection Matte Black Clear Glass Light Kit

Specifications:

- Clear Glass Cylindrical
- Fully dimmable with dimmable bulbs
- Backplate 8.125 in W., 0.5 in ht., 8.125 in depth
- 8 in of wire supplied

Performance:

Number of Lamps	2
Input Power	7 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	600/95 (LM-79)
CCT	2700 K
CRI	90 CRI
Life (hours)	15000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	1 year warranty
Labels	cETLus Dry Location Listed

P260000-31M-WB



Dimensions:

Length: 11-7/8 in
Diameter: 11-7/8 in
Height: 7-1/2 in

Clear Glass Cylindrical
Width: 12 in
Height: 5-3/4 in