

Project:
Fixture Type:

Location:

Contact:

AirPro Dry Location Listed



Description:

Four-light kit with white washed alabaster style glass shades beautiful in design. Innovative spring clip glass attachment system eliminates unsightly excess hardware. Good for use with P2500 and P2501 ceiling fans and includes quick connector for easy wiring. Includes four 3000K, 800 lumen each (source), Title 24 certified LED bulbs. White Finish.


Specifications:

- · Alabaster glass Cone
- · Alabaster style white washed glass shades
- · White finish.
- Good for use with Progress Lighting ceiling fans: P2500, P2501, P2524 and P2525 ceiling fans and P2502 indoors.
- · Innovative spring clip glass attachment system- eliminates hardware.
- Includes four 3000K, 800 lumen each (source), Title 24 certified LED bulbs
- · Fan quick connect wiring.
- · Energy Star Qualified
- · Meets California T24 JA8-2016.
- · Fully dimmable with dimmable bulbs.
- 6 in of wire supplied

Performance:

Number of Lamps	4
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	800/88 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	25000 (L70/TM-21)
EMI/RFI	Title 24
Max. Operating Temp	40 °C
Warranty	1-year Limited Warranty
Labels	UL Dry Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016


P2610-30WB



Dimensions:

Diameter: 15 in Height: 6-1/4 in

Alabaster glass Cone Width: 5-3/8 in Height: 4-7/8 in





AirPro

Universal -use with any indoor fan with 1/8" IPS light kit adapter • Dry Location Listed



Dimming Notes:

P2610-30WB is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Maestro MAELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P2610-30WB