

Project:		
Fixture Type:		
Location:		
Contact:		

WALL CONTROL

Ceiling mounted • Dry location listed

Description:

Four speed ceiling fan wall control. This is a universal switch and will work with most ceiling fans. Not for use with multiple fans.

Specifications:

- · Ivory (-95) (painted)
- · Ivory color
- · 4 Speed Fan control
- · Rated at 1.25amps. 120VAC/60Hz.
- UL Listed
- · Includes wall cover plate
- · Includes wire nuts for the electrical connections
- · Not for use with multiple fans

Performance:

Input Voltage	120 V
Input Frequency	
Warranty	1 Year
Labels	ULus Dry location listed

P2613-95

Images:



Dimensions:

Width: 2-3/4" Depth: 2" Height: 4-5/8"