

## Two-Light Ceiling Fan Light Kit

Ceiling fan light kit mounted • Dry location listed **PROGRESS LED**

### Description:

Elegant alabaster glass ceiling fan light conceals light bulbs and casts an inviting illumination in any size room. Energy saving compact fluorescent light source is a great benefit with this fixture. Corresponding pull chain features Chrome finish with a white fob. Universal style is good for fans that accept an accessory light.

### Specifications:

- Brushed Nickel (-09) (Plated)
- Steel Construction
- Alabaster glass bowl
- Elegant alabaster glass casts an inviting illumination.
- Brushed Nickel finish w/ Chrome pull chain and white fob.
- Compact fluorescent light source.
- Quick-connect wiring to any indoor progress fan that accept an accessory light.
- Not compatible with dimming controls, including dimming remote controls.
- 190-watt limiter
- 6" of wire supplied
- Meets California Title 24 high efficacy requirements

### Performance:

Number of Modules	2
Input Power	13w
Input Voltage	120 V
Warranty	1 year warranty
Labels	UL-CUL Dry location listed Meets California Title 24 high efficacy requirements

## P2621-09EBWB

### Images:



### Dimensions:

Diameter: Diameter: 10-3/4"  
Height: 6"

Glass  
Width: 10-3/4"  
Height: 6"