

Project:
Fixture Type:
Location:

## AirPro

Ceiling fan light kit Mounted • Dry Location Listed PROGRESS LED

Contact:

### **Description:**

Incorporate a ceiling fan lighting kit from the Lindale Collection to make your ceiling fan more versatile. Includes a frosted polycarbonate shade complemented by a satin white finish. Shade is shatterproof and includes a 5-year limited warranty.

#### **Specifications:**

- · Frosted polycarbonate Shade
- · Coated in a satin white finish.
- Ideal for ceiling fans mounted in a great room, bedroom, living room, or bonus room.
- · Includes LED light source.
- · Frosted shatterproof shade.
- · 83 lum/watt with 3000K.
- · Measures 6-7/8-inch width by 2-7/8-inch height.
- · Dry location listed.
- · 5-year limited warranty.
- · Light kit should be used only with P250028.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- · Dimmable to 10% brightness (See Dimming Notes)



Number of Modules	1
Input Power	24 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	2,000/83 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	5-year Limited Warranty
Labels	UL Dry Location Listed
	Meets California Title 24 JA8-2019





#### **Dimensions:**

Diameter: 6-15/16 in Height: 2-15/16 in

Frosted polycarbonate Shade

Width: 6-9/16 in Height: 0-7/8 in



# AirPro

Ceiling fan light kit Mounted • Dry Location Listed PROGRESS LED

#### **Dimming Notes:**

P2669-2830K is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### **Dimming Controls:**

Lutron\_Nova T VTELV-300

Lutron\_Diva DVELV-300P

Lutron\_Diva DVCL-253P

IDevices\_IDEV0009

Lutron\_Toggler TGCL-153PH-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P2669-2830K